

Indicator Lights (Neon, LED and Filament Lamp)



UL file E63363

CSA file LR29381

Colours and voltages:







Neon	Red, Amber, Green, Clear 100/130V (marked 110V), 200/250V (marked 230V)
LED	Red, Yellow, Green 2.0/2.2V Resistors for other voltages available
Filament lamp	Red, Amber, Green, (Clear & Blue check availability) 6V, 12/14V, 24/28V

To create a catalogue number:

Refer to the 2 columns below (terminal and type)

Then state:

Lens colour, voltage and whether neon, LED or filament lamp

TERM	TYPE	PANEL & °C
L	L 2951 00 Chrome bezel available  S D N FI KEMA S UL	∅ 8.0 0.8-1.6 page 66
L	(H) 0568 A(*) Deep lens profile  NEW VDE at T100	∅ 8.0
K 2.8		0.8-3.5
H 4.8		page 66
L	(H) 0568 B(*) Shallow lens profile  NEW VDE at T100	∅ 8.0
K 2.8		0.8-3.5
H 4.8		page 66
L	(L) 0569 AW  NEW	∅ 9.0 0.8-2.5 Call factory
L	(C) 0273 00  S D N FI KEMA S UL	∅ 9.0
K 2.8		2.0 max
H 4.8		page 66
L	(C) 0278 00  S D N FI KEMA S UL	∅ 9.0
K 2.8		2.0 max
H 4.8		page 66
C 6.3		

DIMENSIONS (mm)

